

NEW CLAMP FOR THE TOUCT-3G SMARTlogger™



In June 2009, DENT Instruments introduced a new TOUCT-3G Clamp. The new clamp functions the same as the old clamp, with industry-leading low-end sensitivity and a wide dynamic range. Additionally, the window opening of the new clamp is larger, making it much easier to use with large conductors. No changes need to be made in the setup, deployment or use with the new-style clamp.

If you have any questions about our updated TOUCT-3G, please do not hesitate to contact us (541.388.4774 or info@dentinstruments.com).

