

LIGHTINGLOGGER (TOUL-3G/4G) WITH FIBER OPTIC ATTACHMENT

rev 082211

DENT's LIGHTINGlogger is the fastest way to answer the question, "How long have the lights been on?" The LIGHTINGlogger can be installed in nearly any light fixture with powerful magnets. But what if you're dealing with a fixture where there's no easy access to the light source or you need to isolate one light specifically and tune out the rest?

The answer is the Fiber Optic Attachment (TOU-FO) for the LIGHTINGlogger. This flexible attachment snaps on any 3G or 4G LIGHTINGlogger. Simply bend the attachment so that it points towards the light source you wish to monitor.

The Fiber Optic Attachment is available in custom lengths from 1 foot to 15 feet long. Contact DENT Instruments for more information.

